



JKM02

Multifunction measurement device DIN rail 2x3-Phase RS485

Technical Features

Architecture

Bus system	MODBUS
Type of pole	4P

Capacity

Number of modules	4
-------------------	---

Dimensions

Height	90 mm
Width	70 mm
Depth	62 mm

Equipment

Type of pulse generator	Electrical
-------------------------	------------

Compatibility

Suitable for	Purchase
--------------	----------

Connection

Connector/plug type	Pulse
Bus system	RS485

Installation, mounting

Mounting on	DIN rail
-------------	----------

Measurement

Measuring system	Measurement transformer
Type of measuring instrument	Electronic
Measurement range voltage Ph-N	60 - 300 V
Measurement range voltage Ph-Ph	104 - 520 V
Frequency measuring range	45 - 65 Hz

Functions

Accuracy class	B
Tariff type	One-tariff

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-10 - 55 °C
Storage/transport temperature	-20 - 75 °C

Frequency

Frequency	45 - 65 Hz
-----------	------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes