



JN204B

250A 12 Way 125A Outgoers Plain

Technical Features

Connection

Number of accessible phases	3
-----------------------------	---

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	250 A
---------------	-------

Equipment

With lock	No
-----------	----

Capacity

Number of modules	36
-------------------	----

Functions

Has protection main switch	No
----------------------------	----

Dimensions

Height	1250 mm
Width	710 mm
Depth	178.40 mm

Cover, door

Number of cabinet doors	1
Door/cover is transparent	No

Materials

Material	Steel
RAL code	7035 9001
Colour	Light grey

Safety

Protection class	Isolation class III
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30
Locking type	Key lock Quarter turn lock

Sustainability

RoHS conform	Yes
--------------	-----