



HCW400AR



**Load Break Switch Disconnecter h3+ P630 3P 400A FTC**

**Technical Features**

**Electric current**

|  |       |
|--|-------|
| Rated current  | 400 A |
| Rated short-time withstand current I <sub>cw</sub> IEC 60947 | 5 kA  |

**Architecture**

|                           |        |
|---------------------------|--------|
| Number of poles           | 3      |
| Control/operation element | Toggle |

**Voltage**

|  |        |
|--|--------|
| Rated insulation voltage U <sub>i</sub>          | 800 V  |
| Rated impulse withstand voltage U <sub>imp</sub> | 8000 V |

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

**Functions**

|           |        |
|-----------|--------|
| Trip unit | Switch |
|-----------|--------|

**Sustainability**

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |