



WGCXR131PNB

**10A 3G press round switch;nb**

**Technical Features**

**Electric current**

Switching current 10 A

**Voltage**

Rated voltage 250 V

**Architecture**

Control/operation element Triple rocker

**Materials**

Colour Bronze

Surface finish Matt

Material Polycarbonate (PC)

Treatment Varnished

Transparent No

**Dimensions**

Height 86 mm

Width 86 mm

Depth 25 mm

Built-in depth flush-mounted boxes 35 mm

**Controls and indicators**

Number of buttons 3

**Connectivity**

Type of connection Screw terminal

**Safety**

Ingress Protection (IP) class IP20

**Accessories**

Has labelling field No

**Texts**

Switch mode 1-way

**Suitable for**

shark

**Sustainability**

RoHS conform Yes