



HIB463M

Motorized transfer switch 4P 1600A

Technical Features

Voltage

Rated operational voltage U _e	380 - 415 V
------------------------------------------	-------------

Electric current

Rated current	1600 A
Rated conditional short-circuit current I _{cc} with gl-gG fuses	100 kA

Power

Rated operational power under 400 V AC AC1	1053000 W
--------------------------------------------	-----------

Architecture

Number of poles	4
Device construction type	Fixed built-in

Compatibility

Suitable for DIN Rail	No
Suitable for distribution board	Yes

Installation, mounting

Mounting on	Mounting plate
-------------	----------------