



HWX702H

Spring charging motor 48-60V DC HW1 (MO)

Technical Features

Electric current

Rated current	4.80 A
---------------	--------

Voltage

Type voltage supply	DC
Rated insulation voltage Ui	450 V
Rated impulse withstand voltage Uimp	6000 V
Command voltage DC	48 - 60 V

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes