



HIB463M

Motorized transfer switch 4P 2000A

Technical Features

Voltage

Rated operational voltage U_e 380 - 415 V

Electric current

Rated current 2000 A

Power

Rated operational power under 400 V AC AC1 1316000 W

Architecture

Number of poles 4

Device construction type Fixed built-in

Compatibility

Suitable for DIN Rail No

Suitable for distribution board Yes

Installation, mounting

Mounting on Mounting plate