



47436049

SCHUKO soc. out. "ZSV" imprint in orange, Q.x, p. white velvety

**Technical Features**

**Voltage**

Rated voltage 250 V

**Electric current**

Rated current 16 A

**Frequency**

Frequency 50 - 60 Hz

**Materials**

Colour Polar white

RAL code 9010

Surface finish Velvety

Material Duroplastic

Treatment Untreated

**Dimensions**

Height 71 mm

Width 71 mm

Number of units 1

Built-in depth flush-mounted boxes 31 mm

Built-in depth 32 mm

**Connection**

Connector/plug type Plug-in terminal

**Installation, mounting**

Mounting on Flush mounting

**Connectivity**

Type of connection Plug-in connection

Mounting type Screw mounting

Claw mounting

**Equipment**

Connector/plug type socket outlet SCHUKO

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

With lock No

**Accessories**

Has labelling field No

**Capacity**

Number of modules 1

**Safety**

With enhanced contact protection No

Impact resistance IK IK02

Ingress Protection (IP) class IP20

**Functions**

With orientation lighting No

With function lighting No

**Texts**

Imprint With imprint "ZSV"

Cover Central cover plate

---

**Texts**

Protection	Without enhanced contact protection
Type of connection	With plug-in terminals

---

**Suitable for**

Q.x

---

**Sustainability**

RoHS conform	Yes
--------------	-----