



LNH0100M

HRC LV fuse NH000 gG AC500V 100A double indicator with live gripping-lugs

Technical Features

Architecture

Curve	gG
-------	----

Fuse

Fuse size	NH000
-----------	-------

Fuse characteristics	gG
----------------------	----

Voltage

Type voltage supply	AC/DC
---------------------	-------

Electric current

Rated current	100 A
---------------	-------

Use conditions

Insulated	No
-----------	----

Main electrical attributes

Rated short-circuit breaking capacity I _{cn} AC according to IEC 60898-1	120 kA
---	--------

Power

Total power loss under I _N	7.50 W
---------------------------------------	--------

Dimensions

Height	58.50 mm
--------	----------

Width	21 mm
-------	-------

Depth	79 mm
-------	-------

Sustainability

Halogen free	Yes
--------------	-----

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----