



WPPS12R



**10AX Push Switch & Back Box with Knockouts**

**Technical Features**

**Electric current**

Momentary contact current 10 A

**Voltage**

Rated voltage 250 V

**Architecture**

Number of poles 2

**Materials**

Colour Grey

Surface finish Glossy

Material Metal

Treatment Epoxy

Transparent No

**Dimensions**

Height 86 mm

Width 86 mm

Depth 53.20 mm

**Installation, mounting**

Mounting on Surface mounting

**Controls and indicators**

Number of buttons 1

Type of push button Single push button

With feedback signal contact No

**Connectivity**

Type of connection Screw terminal

**Safety**

Ingress Protection (IP) class IP20

**Accessories**

Has labelling field No

**Texts**

Imprint Without imprint

Installation mode For wall mounting

Switch mode NO contact

**Sustainability**

REACH-SVHC free Yes

RoHS conform Yes