



HWX701H

Spring charging motor 24V DC HW1 (MO)

Technical Features

Electric current

Rated current	9.60 A
---------------	--------

Voltage

Type voltage supply	DC
Rated insulation voltage U_i	450 V
Rated impulse withstand voltage U_{imp}	6000 V
Command voltage DC	24 - 24 V

Use conditions

Operating temperature	-25 - 70 °C
-----------------------	-------------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes