



WGCXHSRKB

115/230V shaver socket;kb

Technical Features

Electric current

| | |
|----------------|--------|
| Rated current | 0.08 A |
| Output current | 0 mA |

Voltage

| | |
|-----------------|-----------|
| Rated voltage | 250 V |
| Nominal voltage | 220-250 V |
| Output voltage | 0-0 V |

Use conditions

| | |
|-----------------------|-----------|
| Operating temperature | -20-45 °C |
|-----------------------|-----------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Power

| | |
|---------------------------|-----|
| Output power | 0 W |
| Power consumption standby | 0 W |

Materials

| | |
|--|--------------------|
| Colour | Knight black |
| Surface finish | Matt |
| Material | Polycarbonate (PC) |
| Treatment | Coated |
| Contains recycled material (% of total plastic weight) | 0 % |

Dimensions

| | |
|------------------------------------|-------|
| Height | 86 mm |
| Width | 86 mm |
| Depth | 45 mm |
| Built-in depth flush-mounted boxes | 47 mm |
| Built-in depth | 45 mm |

Connection

| | |
|--|--------------------------|
| Connector/plug type | NEMA |
| Cross-section flexible conductor without wire end sleeve | 0.08 - 4 mm ² |

Installation, mounting

| | |
|-------------------------------|----------------|
| Mounting on | Flush mounting |
| Mounting-/Connection Position | Back |

Connectivity

| | |
|-------------------------|------------------|
| Type of connection | Screw terminal |
| With claw mounting | No |
| Mounting type | Screw mounting |
| Connector/plug type USB | British Standard |

Equipment

| | |
|-----------------------------------|------------------|
| Connector/plug type socket outlet | British Standard |
| Rotated central insert | No |
| With hinged lid | No |
| With round protective earth pin | No |
| With signal lamp | No |
| With lock | No |

Accessories

| | |
|---------------------|------|
| Has labelling field | No |
| Pre-equipped with | None |

| | |
|----------------------------------|------|
| Capacity | |
| Number of modules | 0 |
| Safety | |
| With enhanced contact protection | No |
| Impact resistance IK | IK02 |
| Ingress Protection (IP) class | IP20 |
| Functions | |
| With orientation lighting | No |
| With function lighting | No |
| Identification | |
| With imprint | No |
| Suitable for | |
| shark | |
| Sustainability | |
| RoHS conform | Yes |