



HIB463M

Motorized transfer switch 4P 3200A

Technical Features

Voltage

Rated operational voltage U_e	380 - 415 V
---------------------------------	-------------

Electric current

Rated current	3200 A
---------------	--------

Power

Rated operational power under 400 V AC AC1	2106000 W
--	-----------

Architecture

Number of poles	4
Device construction type	Fixed built-in

Compatibility

Suitable for DIN Rail	No
Suitable for distribution board	Yes

Installation, mounting

Mounting on	Mounting plate
-------------	----------------