



WGCHRCASV

RCA+S-VIDEO socket

Technical Features

Connection

Connector/plug type	Cinch S-video
---------------------	------------------

Frequency

Frequency video	160 MHz
Audio frequency	20 - 20000 Hz

Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)

Dimensions

Height	86 mm
Width	86 mm
Depth	46 mm
Built-in depth flush-mounted boxes	47 mm

Connectivity

Direction of outlet of data socket	Back
Mounting type	Screw mounting

Equipment

With dust cover	No
-----------------	----

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Texts

Labelling	Without labelling field
Supporting plate/supporting ring	With supporting ring

Suitable for

shark	
-------	--

Sustainability

RoHS conform	Yes
--------------	-----