



WGCHRCASV

**RCA+S-VIDEO socket**

**Technical Features**

**Connection**

|                     |                  |
|---------------------|------------------|
| Connector/plug type | Cinch<br>S-video |
|---------------------|------------------|

**Frequency**

|                 |               |
|-----------------|---------------|
| Frequency video | 160 MHz       |
| Audio frequency | 20 - 20000 Hz |

**Materials**

|                |                    |
|----------------|--------------------|
| Colour         | White              |
| Surface finish | Glossy             |
| Material       | Polycarbonate (PC) |

**Dimensions**

|                                    |       |
|------------------------------------|-------|
| Height                             | 86 mm |
| Width                              | 86 mm |
| Depth                              | 46 mm |
| Built-in depth flush-mounted boxes | 47 mm |

**Connectivity**

|                                    |                |
|------------------------------------|----------------|
| Direction of outlet of data socket | Back           |
| Mounting type                      | Screw mounting |

**Equipment**

|                 |    |
|-----------------|----|
| With dust cover | No |
|-----------------|----|

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Texts**

|                                  |                         |
|----------------------------------|-------------------------|
| Labelling                        | Without labelling field |
| Supporting plate/supporting ring | With supporting ring    |

**Suitable for**

|       |  |
|-------|--|
| shark |  |
|-------|--|

**Sustainability**

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|