




SL200553D3

Vanjski ugao, podesiv, bezhalogeni, SL 20x55 mm, Dekor javor

Tehničke karakteristike

Pribor

Vrsta pribora	Oblikovano/kalupljeno
---------------	-----------------------

Postavke

Ugaoni domet	83 - 135
--------------	----------

Dimenzije

Visina	55 mm
Širina	20 mm

Materijali

Materijal	Akrilonitril butadien stiren (ABS)
Boja	Javor

Sigurnost

Ingress Protection (IP) klasa	IP40
Otpornost na udarce IK	IK07

Održivost

REACH-bez SVHC	Da
Usklađeno sa RoHS	Da

Ilustracije / crteži

