



20347103

Thermostat, NO contact,Cen. plate,f. heat.,rocker switch,ext.temp.sen.,K5,al.

Technical Features

Architecture

Control/operation element Rotative

Electric current

Rated current 10 A

Max. switching current 10 A

Voltage

Nominal voltage 230 - 230 V

Power supply

Supply voltage 230 V AC

Frequency

Frequency 50 - 60 Hz

Settings

Comfort temperature setpoint 10 - 50 °C

Materials

Colour Aluminium

RAL code 9006

Surface finish Matt

Material Metal
Plastic

Dimensions

Height 71 mm

Width 71 mm

Depth 54.5 mm

Screen

With display No

Equipment

Switching temperature difference 1 K

Type of thermostat Regulator of heating floor

Type of probe Floor heating probe

Safety

Ingress Protection (IP) class IP20

Connection

Type of contacts 1NO

Compatibility

Type of HVAC control Heating

Use conditions

Energy efficiency class I (1%)

Texts

Installation mode Without spreader claws

Type of connection With plug-in terminals

Thermal re-circulation With thermal return

Imprint With imprint

Junction With separate connection for night lowering

Sustainability

REACH-SVHC free Yes