




SL200803D2

Vanjski ugao, podesiv, SL 20080, Dekor bukva

Tehničke karakteristike

Pribor

Vrsta pribora	Oblikovano/kalupljeno
---------------	-----------------------

Postavke

Ugaoni domet	83 - 135
--------------	----------

Dimenzije

Visina	80 mm
Širina	20 mm

Materijali

Materijal	Akrilonitril butadien stiren (ABS)
Boja	Bukva

Sigurnost

Ingress Protection (IP) klasa	IP40
Otpornost na udarce IK	IK07

Održivost

REACH-bez SVHC	Da
Usklađeno sa RoHS	Da

Ilustracije / crteži

