



383803



Group spring-return push-button 2p, with neutral-pos., Serie 1930/Glas/R.classic

Technical Features

Electric current

| | |
|---------------------------|------|
| Switching current | 10 A |
| Momentary contact current | 10 A |

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Architecture

| | |
|---------------------------|---------------------|
| Control/operation element | Short rotary handle |
| Number of poles | 2 |

Materials

| | |
|-------------|------------------|
| Material | Metal Plastic |
| Transparent | No |

Dimensions

| | |
|------------------------------------|-------|
| Height | 71 mm |
| Width | 71 mm |
| Depth | 42 mm |
| Built-in depth flush-mounted boxes | 35 mm |

Installation, mounting

| | |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Controls and indicators

| | |
|------------------------------|-------------------|
| Number of buttons | 0 |
| Type of push button | Group push button |
| With feedback signal contact | No |

Connectivity

| | |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
| Impact resistance IK | IK07 |

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Texts

| | |
|--------------------|-----------------------|
| Imprint | Without imprint |
| Switch mode | With neutral position |
| Type of connection | With screw terminals |

Suitable for

| |
|---|
| Serie 1930 / Serie Glas / Serie R.classic |
|---|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|