



383803

**Group spring-return push-button 2p, with neutral-pos., Serie 1930/Glas/R.classic**

**Technical Features**

**Electric current**

Switching current	10 A
Momentary contact current	10 A

**Voltage**

Rated voltage	250 V
---------------	-------

**Architecture**

Control/operation element	Short rotary handle
Number of poles	2

**Materials**

Material	Metal Plastic
Transparent	No

**Dimensions**

Height	71 mm
Width	71 mm
Depth	42 mm
Built-in depth flush-mounted boxes	35 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Controls and indicators**

Number of buttons	0
Type of push button	Group push button
With feedback signal contact	No

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

**Safety**

Ingress Protection (IP) class	IP20
Impact resistance IK	IK07

**Texts**

Imprint	Without imprint
Switch mode	With neutral position
Type of connection	With screw terminals

**Suitable for**

Serie 1930 / Serie Glas / Serie R.classic
---

**Sustainability**

RoHS conform	Yes
--------------	-----