




1084608900

**Centre plate rotary knob 3-step switch, Berker Q.x, polar white velvety**

**Technical Features**

**Architecture**

|                           |          |
|---------------------------|----------|
| Control/operation element | Rotative |
|---------------------------|----------|

**Materials**

|                |             |
|----------------|-------------|
| Colour         | Polar white |
| RAL code       | 9010        |
| Surface finish | Velvety     |
| Material       | Duroplastic |
| Treatment      | Untreated   |

**Dimensions**

|        |          |
|--------|----------|
| Height | 58.80 mm |
| Width  | 58.80 mm |
| Depth  | 30.50 mm |

**Connectivity**

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

**Equipment**

|                                |    |
|--------------------------------|----|
| Monitoring window/light outlet | No |
|--------------------------------|----|

**Accessories**

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Texts**

|                   |                     |
|-------------------|---------------------|
| Imprint           | With imprint        |
| Installation mode | For screw fastening |

**Suitable for**

|     |  |
|-----|--|
| Q.x |  |
|-----|--|

**Sustainability**

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |