



VM_SIZE_6

Design 30 , 10 way Configureable HI 100A Sw 2*100A 30mA RCCB Type A KO SPD

Technical Features

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Architecture

| | |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

Functions

| | |
|----------------------------|-----|
| Has protection main switch | Yes |
| Overvoltage protection | Yes |

Installation, mounting

| | |
|----------------------------|----|
| Suitable for outdoor usage | No |
|----------------------------|----|

Capacity

| | |
|-------------------|----|
| Number of modules | 10 |
|-------------------|----|

Electric current

| | |
|---------------|-------|
| Rated current | 100 A |
|---------------|-------|

Dimensions

| | |
|-----------------------|-----------|
| Depth | 102.50 mm |
| Height | 240 mm |
| Width | 400 mm |
| Thickness of sidewall | 1 mm |

Cover, door

| | |
|---------------------------|----|
| Interlockable | No |
| Door/cover is transparent | No |

Materials

| | |
|----------|------------|
| RAL code | 9010 |
| Colour | Pure white |
| Material | Steel |

Connection

| | |
|-----------------------------|---|
| Number of accessible phases | 1 |
|-----------------------------|---|

Scope of delivery

| | |
|--|---|
| Number of earth leakage circuit breaker type A | 2 |
| Number of RCCB in enclosure | 2 |

Equipment

| | |
|--------------------|----|
| Number of rows | 1 |
| Number of rails | 1 |
| Extension possible | No |
| With socket outlet | No |

Safety

| | |
|-------------------------------|-------|
| Impact resistance IK | IK05 |
| Ingress Protection (IP) class | IP2XC |

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|