



SVS132B



**Red Ind. light 12/48V QC busbar passing**

**Technical Features**

**Capacity**

Number of modules	1
-------------------	---

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Voltage**

Rated insulation voltage $U_i$	250 V
Rated impulse withstand voltage $U_{imp}$	2000 V
Rated operational voltage $U_e$	12 - 48 V
Type voltage supply	AC/DC

**Use conditions**

Operating temperature	-20 - 50 °C
Storage/transport temperature	-40 - 80 °C

**Connectivity**

Type of connection	quickconnect
--------------------	--------------

**Connection**

Cross-section flexible conductor	1.5 - 2.5 mm <sup>2</sup>
Cross-section rigid conductor	1.5 - 2.5 mm <sup>2</sup>

**Power**

Total power loss under IN	0.33 W
---------------------------	--------

**Dimensions**

Height	83 mm
Width	17.50 mm
Depth	62 mm

**Lighting**

Type of lamp	LED
--------------	-----

**Connection**

Type of lamp socket	Fix
---------------------	-----

**Materials**

Colour	Red
--------	-----

**Safety**

Ingress Protection (IP) class	IP20
-------------------------------	------

**Power**

Power per charging point	0 kW
--------------------------	------

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

