



LFS6006009016

Trunking LFS made of steel 60x60mm in traffic white

Technical Features

Dimensions

Height	60 mm
Width	60 mm
Length	2000 mm
Inner cross-section	2860 - 2860 mm ²

Capacity

Max. number of cables (Ø11mm, 50% filled, without devices)	12
--	----

Materials

Material	Steel
Treatment	Varnished
RAL code	9016
Colour	Traffic white

Safety

Impact resistance IK	IK08
Ingress Protection (IP) class	IP30

Standards

Suitable for functional integrity according to DIN4102-12	No
---	----

Use conditions

Operating temperature	-5 - 90 °C
-----------------------	------------

Connectivity

Trunking coupling	Couplers as separate reference
-------------------	--------------------------------

Equipment

Number of partitions	0
Number of compartments	1 - 1
Number of pluggable partitions	0
Cable retaining clip included	Yes
With protective film	No

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes

Illustrations | Drawings

