



VE412PN

Enclosure,vector,surface mounted,IP65,48M,UV stable,with metric cable entry

### Technical Features

#### Voltage

Nominal voltage	400 - 400 V
Rated operational voltage in DC	1000 - 1000 V

#### Installation, mounting

Suitable for outdoor usage	Yes
Mounting on	Surface mounting

#### Electric current

Rated current	63 A
---------------	------

#### Equipment

Number of rails	4
Number of rows	4
Number of section in width	1
With lock	No
Has neutral terminal block	No

#### Capacity

Number of modules	48
-------------------	----

#### Functions

With conduit inlets	Yes
---------------------	-----

#### Dimensions

Height	677 mm
Width	310 mm
Depth	151 mm

#### Cover, door

Number of cabinet doors	1
Number of locks	0

#### Dimensions

Number of width units	12
-----------------------	----

#### Cover, door

Door/cover is transparent	Yes
---------------------------	-----

#### Connection

Number of conduit inlets	12
--------------------------	----

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Materials

Material	Polycarbonate (PC)
RAL code	7035
Colour	Light grey

#### Equipment

Has earthing terminal block	No
Has mounting plate	No

#### Materials

Ultraviolet-resistant	Yes
-----------------------	-----

#### Safety

Protection class	Isolation class II
Impact resistance IK	IK08
Ingress Protection (IP) class	IP65

<b>Safety</b>	
Locking type	Snap on lock
	Without lock
Glow wire test	850 °C
<b>Sustainability</b>	
RoHS conform	Yes