




936552568

Series switch, common input terminal, Integro - Design Flow/Pure, chr m, lacq

Technical Features

Electric current

Switching current	16 A
-------------------	------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	Chrome
RAL code	9006
Surface finish	Matt
Material	Thermoplastic
Treatment	Chrome plated Varnished

Identification

Assembly arrangement	Basic element with central cover plate
----------------------	--

Connectivity

Mounting type	Built in installation Screw mounting
---------------	---

Controls and indicators

Number of buttons	2
-------------------	---

Dimensions

Dimensions	55.50 x 55.50 mm
Built-in depth	10 mm
Built-in depth flush-mounted boxes	13 mm

Safety

Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

Architecture

Control/operation element	Double rocker
---------------------------	---------------

Electric current

Rated current	10 A
---------------	------

Texts

Installation mode	For screw fastening
Type of connection	With screw terminals
Lighting	Without lighting (cannot be illuminated)
Switch mode	Series

Sustainability

RoHS conform	Yes
--------------	-----