




936552568

Series switch, common input terminal, Integro - Design Flow/Pure, chr m, lacq

Technical Features

Electric current	
Switching current	16 A

Voltage	
Rated voltage	250 V

Materials	
Colour	Chrome
RAL code	9006
Surface finish	Matt
Material	Thermoplastic
Treatment	Chrome plated Varnished

Identification	
Assembly arrangement	Basic element with central cover plate

Connectivity	
Mounting type	Built in installation Screw mounting

Controls and indicators	
Number of buttons	2

Dimensions	
Dimensions	55.50 x 55.50 mm
Built-in depth	10 mm
Built-in depth flush-mounted boxes	13 mm

Safety	
Ingress Protection (IP) class	IP20
Impact resistance IK	IK05

Architecture	
Control/operation element	Double rocker

Electric current	
Rated current	10 A

Texts	
Installation mode	For screw fastening
Type of connection	With screw terminals
Lighting	Without lighting (cannot be illuminated)
Switch mode	Series

Sustainability	
RoHS conform	Yes