



1678

LED lamp E10, light control, white

Technical Features

Voltage

Nominal voltage 230 - 230 V

Electric current

Rated current 0 A

Dimensions

Height 9.70 mm

Width 9.70 mm

Depth 29 mm

Materials

Colour White

Lighting

Type of lamp LED

Use conditions

Operating temperature -40 - 70 °C

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes