



1678

LED lamp E10, light control, white

Technical Features

Voltage

Nominal voltage	230 - 230 V
-----------------	-------------

Electric current

Rated current	0 A
---------------	-----

Dimensions

Height	9.70 mm
Width	9.70 mm
Depth	29 mm

Materials

Colour	White
--------	-------

Lighting

Type of lamp	LED
--------------	-----

Use conditions

Operating temperature	-40 - 70 °C
-----------------------	-------------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes