



LNH2200M

HRC LV fuse NH2C gG AC500V 200A double indicator with live gripping-lugs

Technical Features

Architecture

Curve	gG
-------	----

Fuse

Fuse size	NH2C
-----------	------

Fuse characteristics	gG
----------------------	----

Voltage

Type voltage supply	AC/DC
---------------------	-------

Rated operational voltage Ue	500 - 500 V
------------------------------	-------------

Rated voltage at AC 50 Hz	500 - 500 V
---------------------------	-------------

Electric current

Rated current	200 A
---------------	-------

Use conditions

Insulated	No
-----------	----

Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	120 kA
---	--------

Power

Total power loss under IN	18.50 W
---------------------------	---------

Dimensions

Height	150 mm
--------	--------

Width	39 mm
-------	-------

Depth	72.5 mm
-------	---------

Sustainability

Halogen free	Yes
--------------	-----

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----