



WPDP84FON

**20A Double Pole Switch with LED Indicator and Flex Outlet & Back**

**Technical Features**

**Installation, mounting**

Mounting on Surface mounting

**Voltage**

Rated voltage 250 V

**Materials**

Colour Grey

Surface finish Glossy

Material Steel

Treatment Epoxy

**Identification**

Assembly arrangement Basic element with complete housing

**Connectivity**

Mounting type Screw mounting

**Controls and indicators**

Number of buttons 1

**Dimensions**

Dimensions 86 x 86 mm

Built-in depth 0 mm

**Safety**

Ingress Protection (IP) class IP20

**Architecture**

Control/operation element Single rocker

**Electric current**

Rated current 20 A

**Texts**

Lighting With control LED for ON

Switch mode 2-pole