



WMPS12RW

### Push Switch Wide Rocker Grey

#### Technical Features

##### Electric current

|                           |      |
|---------------------------|------|
| Switching current         | 10 A |
| Momentary contact current | 10 A |

##### Voltage

|               |       |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

##### Architecture

|                 |   |
|-----------------|---|
| Number of poles | 2 |
|-----------------|---|

##### Materials

|                |                   |
|----------------|-------------------|
| Colour         | White             |
| Surface finish | Glossy            |
| Material       | Urea formaldehyde |
| Treatment      | Coated            |
| Transparent    | No                |

##### Dimensions

|        |       |
|--------|-------|
| Height | 86 mm |
| Width  | 86 mm |
| Depth  | 24 mm |

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

##### Controls and indicators

|                              |                    |
|------------------------------|--------------------|
| Number of buttons            | 1                  |
| Type of push button          | Single push button |
| With feedback signal contact | No                 |

##### Connectivity

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
|--------------------|----------------|

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

##### Accessories

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

##### Texts

|                   |                                            |
|-------------------|--------------------------------------------|
| Imprint           | Without imprint                            |
| Installation mode | For flush-mounted and hollow wall mounting |
| Switch mode       | NO contact                                 |

##### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |