



936552528

Series switch, common input terminal, Integro - Design Flow/Pure, chr m, galv

Technical Features

Electric current

Switching current 16 A

Voltage

Rated voltage 250 V

Materials

Colour Chrome
RAL code 9006
Surface finish Matt
Material Thermoplastic
Treatment Chrome plated
Coated

Identification

Assembly arrangement Basic element with central cover plate

Connectivity

Mounting type Built in installation
Screw mounting

Controls and indicators

Number of buttons 2

Dimensions

Dimensions 55.50 x 55.50 mm
Built-in depth 10 mm
Built-in depth flush-mounted boxes 13 mm

Safety

Ingress Protection (IP) class IP20
Impact resistance IK IK05

Architecture

Control/operation element Double rocker

Electric current

Rated current 10 A

Texts

Installation mode For screw fastening
Type of connection With screw terminals
Lighting Without lighting (cannot be illuminated)
Switch mode Series

Sustainability

RoHS conform Yes