



VE312F

vector,IP65,48M,UV-stabil,DC/AC,with knockouts

**Technical Features**

**Voltage**

Nominal voltage 400 - 400 V

**Installation, mounting**

Suitable for outdoor usage Yes

Mounting on Surface mounting

**Electric current**

Rated current 63 A

**Equipment**

Number of rails 4

Number of rows 4

Number of section in width 1

With lock No

**Capacity**

Number of modules 48

**Functions**

With conduit inlets Yes

**Dimensions**

Height 677 mm

Width 310 mm

Depth 151 mm

**Cover, door**

Number of cabinet doors 1

Number of locks 0

**Dimensions**

Number of width units 48

**Cover, door**

Door/cover is transparent Yes

**Connection**

Number of conduit inlets 12

**Materials**

Material Plastic

RAL code 7035

Colour Light grey

**Equipment**

Has mounting plate No

**Materials**

Ultraviolet-resistant Yes

**Safety**

Protection class Isolation class II

Impact resistance IK IK08

Ingress Protection (IP) class IP65

Locking type Snap on lock  
Without lock

Glow wire test 850 °C

**Sustainability**

RoHS conform Yes