



WMDP85N

20A Double Pole Switch with LED Indicator Marked WATERHEATER

Technical Features

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	250 V
---------------	-------

Materials

Colour	White
Surface finish	Glossy
Material	Urea formaldehyde
Treatment	Untreated

Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	86 x 86 mm
Built-in depth	21.90 mm

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Architecture

Control/operation element	Single rocker
---------------------------	---------------

Electric current

Rated current	20 A
---------------	------

Texts

Lighting	With control LED for ON
Switch mode	2-pole