



TRE202



**Module 2 outputs 10A IP55 KNX radio Quicklink**

**Technical Features**

**Connectivity**

Radio protocol	KNX Radio
----------------	-----------

**Settings**

Supported configuration mode	ETS easy quicklink
------------------------------	--------------------------

**Connectivity**

Receiver category	2
With bus system KNX	No
With bus system KNX radio	Yes

**Dimensions**

Dimensions	35 x 85 mm
Height	35 mm
Width	85 mm
Built-in depth	40 mm

**Electric current**

Rated current	10 A
---------------	------

**Materials**

Colour	White
--------	-------

**Equipment**

Radio frequency bidirectional	Yes
With switch for manual switch	No

**Electric current**

Switching current	10 A
-------------------	------

**Frequency**

Frequency	50 - 50 Hz
Radio reception frequency	868.30 - 868.30 MHz

**Power**

Output power	2300 W
230 V incandescent and halogen lamp	1500 W

**Voltage**

Operating voltage	230 - 230 V
System supply voltage	230 V AC
Operating voltage over bus	21 - 32 V

**Safety**

Ingress Protection (IP) class	IP55
-------------------------------	------

**Use conditions**

Operating temperature	-10 - 55 °C
-----------------------	-------------

**Texts**

Function	Easy additional functions: +6 scenes Repeat function can be activated to increase the radio range Reset function (to factory setting)
Type of connection	With screw-in lift terminals