



HWX704H

**Spring charging motor 200-250V DC HW1 (MO)**

**Technical Features**

**Electric current**

Rated current	1 A
---------------	-----

**Voltage**

Type voltage supply	DC
Rated insulation voltage $U_i$	450 V
Rated impulse withstand voltage $U_{imp}$	6000 V
Command voltage DC	200 - 250 V

**Use conditions**

Operating temperature	-25 - 70 °C
-----------------------	-------------

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes