



29518982



LED signal light, RGB, S.1, white glossy

Technical Features

Voltage

Rated voltage 230 V

Power

Power absorbed 2 W

Frequency

Frequency 50 - 60 Hz

Lighting

Type of lamp LED

Materials

Colour White
RAL code 1013
Surface finish Glossy
Material Metal
Plastic
Treatment Untreated

Dimensions

Height 70 mm
Width 70 mm
Depth 50 mm

Connection

Conductor cross-section 2.50 - 2.50 mm²

Safety

Ingress Protection (IP) class IP20

Texts

Lighting Light colours cold white, warm white, blue, orange, red, green, purple (magenta) and colour sequence callable via push-button
Colour sequence can be stopped at any position via the push-button.
Labelling Foils with imprint of symbols insertable
Imprint Without imprint