



WNA021

cubyko Push-button 10/1F illuminated composable grey IP55

Technical Features

Electric current

| | |
|---------------------------|------|
| Momentary contact current | 10 A |
|---------------------------|------|

Voltage

| | |
|---------------|-------|
| Rated voltage | 250 V |
|---------------|-------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Architecture

| | |
|---------------------------|--------|
| Control/operation element | Rocker |
|---------------------------|--------|

Materials

| | |
|----------------|----------------------|
| Colour | Grey |
| Surface finish | Matt Satin finish |
| Material | Thermoplastic |
| Treatment | Untreated |
| Transparent | No |

Dimensions

| | |
|------------------------------------|-------|
| Height | 55 mm |
| Width | 55 mm |
| Depth | 41 mm |
| Built-in depth flush-mounted boxes | 40 mm |

Installation, mounting

| | |
|-------------|------------------------------------|
| Mounting on | Flush mounting Surface mounting |
|-------------|------------------------------------|

Controls and indicators

| | |
|------------------------------|--------------------|
| Number of buttons | 1 |
| Type of push button | Single push button |
| With feedback signal contact | No |

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP55 |
| Impact resistance IK | IK05 |

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -15 - 30 °C |
|-----------------------|-------------|

Texts

| | |
|--------------------|-----------------------------------------------------------------|
| Imprint | Without imprint |
| Installation mode | For screw fastening |
| Lighting | With blue 230 V LED unit For lighting and monitoring circuit |
| Type of connection | With N-terminal With plug-in terminals |

Suitable for

| | |
|--------------|--|
| Hager cubyko | |
|--------------|--|

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|