



WNA021



cubyko Push-button 10/1F illuminated composable grey IP55

Technical Features

Electric current

Switching current	10 A
Momentary contact current	10 A

Voltage

Rated voltage	250 V
---------------	-------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Architecture

Control/operation element	Rocker
---------------------------	--------

Materials

Colour	Grey
Surface finish	Matt Satin finish
Material	Thermoplastic
Treatment	Untreated
Transparent	No
Backside internal	Matt

Dimensions

Height	55 mm
Width	55 mm
Depth	41 mm
Built-in depth flush-mounted boxes	40 mm

Installation, mounting

Mounting on	Flush mounting Surface mounting
-------------	------------------------------------

Controls and indicators

Indicator lamp	As an accessory
Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

Connection

Connector/plug type	Turn screw lock
---------------------	-----------------

Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK05

Accessories

Has labelling field	No
---------------------	----

Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

Texts

Installation mode	For screw fastening
Lighting	With blue 230 V LED unit For lighting and monitoring circuit
Switch mode	Change-over
Type of connection	With N-terminal With plug-in terminals

Suitable for

cubyko

Sustainability

REACH-SVHC free

Yes
