



41101913



**SCHUKO soc.out. LED+"SV" impr.,labfield,enhncd contact prot., S1/B3/7een**

**Technical Features**

**Voltage**

Rated voltage	250 V
---------------	-------

**Electric current**

Rated current	16 A
---------------	------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Materials**

Colour	Green
RAL code	6029
Surface finish	Matt
Material	Thermoplastic
Treatment	Untreated

**Dimensions**

Height	71 mm
Width	71 mm
Built-in depth flush-mounted boxes	31 mm
Built-in depth	32 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Connectivity**

Type of connection	Screw terminal
Mounting type	Screw mounting Claw mounting

**Equipment**

Connector/plug type socket outlet	SCHUKO
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

**Accessories**

Has labelling field	Yes
---------------------	-----

**Capacity**

Number of modules	1
-------------------	---

**Controls and indicators**

Type of lighting for the installation devices	Integrated operating control light
---	------------------------------------

**Safety**

With enhanced contact protection	Yes
Ingress Protection (IP) class	IP20

**Functions**

With orientation lighting	No
With function lighting	Yes

**Texts**

Imprint	With imprint "SV"
Cover	Central cover plate
Protection	Enhanced contact protection
Type of connection	With screw-in lift terminals

---

**Suitable for**

S.x/B.x

---

**Sustainability**

RoHS conform

Yes