



WNA025

cubyko PB 1F w. FPL compos. grey

### Technical Features

#### Electric current

Momentary contact current	10 A
---------------------------	------

#### Voltage

Rated voltage	250 V
---------------	-------

#### Frequency

Frequency	50 - 60 Hz
-----------	------------

#### Architecture

Control/operation element	Rocker
---------------------------	--------

#### Materials

Colour	Grey
Surface finish	Matt Satin finish
Material	Thermoplastic
Treatment	Untreated
Transparent	No

#### Dimensions

Height	70.90 mm
Width	70.90 mm
Depth	41.50 mm
Built-in depth flush-mounted boxes	40 mm

#### Installation, mounting

Mounting on	Flush mounting Surface mounting
-------------	------------------------------------

#### Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

#### Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK05

#### Use conditions

Operating temperature	-25 - 35 °C
-----------------------	-------------

#### Texts

Imprint	With imprint
Installation mode	For screw fastening
Lighting	With blue 230 V LED unit
Terminal	Wago clip-in 3-wire connection terminal for wiring
Type of connection	With N-terminal With plug-in terminals

#### Suitable for

Hager cubyko
--------------

#### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes