



FD52GN

Enclosure, NewVegaD, 900x550x193mm, 120 modules, surface-mounted, empty

Technical Features

Dimensions

Height	900 mm
Width	550 mm
Depth	193 mm
Thickness of sidewall	1 mm

Safety

Ingress Protection (IP) class	IP30
Protection class	Isolation class II
Locking type	Without lock
Impact resistance IK	IK07

Equipment

Number of flange plate openings	2
---------------------------------	---

Installation, mounting

Mounting on	Surface mounting
Suitable for outdoor usage	No

Materials

Colour	Pure white
RAL code	9010
Treatment	Powder coated
Material	Metal Plastic

Equipment

Number of rows	5
----------------	---

Cover, door

Number of cabinet doors	0
Door/cover is transparent	No

Electric current

Rated current	160 A
---------------	-------

Sustainability

RoHS conform	Yes
--------------	-----