



TRE302



### RF external double push button wall mounted

#### Technical Features

##### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

##### Use conditions

Operating temperature	-10 - 55 °C
-----------------------	-------------

##### Frequency

Radio transmission frequency	868.30 MHz
------------------------------	------------

##### Connectivity

Receiver category	2
Radio protocol	KNX Radio

##### Functions

With room temperature controller	No
----------------------------------	----

##### Voltage

Operating voltage	3 - 3 V
-------------------	---------

##### Dimensions

Built-in depth flush-mounted boxes	25 mm
Height	76 mm
Width	49 mm

##### Materials

Colour	White
RAL code	9010
Material	Plastic
Surface finish	Glossy Matt

##### Accessories

Has labelling field	No
---------------------	----

##### Texts

Function	Easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control Configuration can simply be transferred from a master device Reset function (to factory setting)
Installation mode	For screw fastening or For mounting with adhesive mounting For vertical and horizontal mounting

##### Sustainability

RoHS conform	Yes
--------------	-----