



TRE301



RF external single push button wall mounted

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Use conditions

Operating temperature	-10 - 55 °C
-----------------------	-------------

Frequency

Radio transmission frequency	868.30 MHz
------------------------------	------------

Connectivity

Receiver category	2
Radio protocol	KNX Radio

Functions

With room temperature controller	No
----------------------------------	----

Voltage

Operating voltage	3 - 3 V
-------------------	---------

Dimensions

Built-in depth flush-mounted boxes	25 mm
Height	76 mm
Width	49 mm

Materials

Colour	White
RAL code	9010
Material	Plastic
Surface finish	Glossy Matt

Accessories

Has labelling field	No
---------------------	----

Texts

Function	Easy additional functions: +6 scenes, on/off operating mode, 1 up/down button control Configuration can simply be transferred from a master device Reset function (to factory setting)
Installation mode	For screw fastening or For mounting with adhesive mounting For vertical and horizontal mounting

Sustainability

RoHS conform	Yes
--------------	-----