



WNA020

### cubyko Push-button 1F composable grey IP55

#### Technical Features

##### Electric current

Momentary contact current	10 A
---------------------------	------

##### Voltage

Rated voltage	250 V
---------------	-------

##### Frequency

Frequency	50 - 60 Hz
-----------	------------

##### Architecture

Control/operation element	Rocker
---------------------------	--------

##### Materials

Colour	Grey
Surface finish	Matt Satin finish
Material	Thermoplastic
Treatment	Untreated
Transparent	No

##### Dimensions

Height	70.90 mm
Width	70.90 mm
Depth	41.50 mm
Built-in depth flush-mounted boxes	40 mm

##### Installation, mounting

Mounting on	Flush mounting Surface mounting
-------------	------------------------------------

##### Controls and indicators

Number of buttons	1
Type of push button	Single push button
With feedback signal contact	No

##### Safety

Ingress Protection (IP) class	IP55
Impact resistance IK	IK05

##### Use conditions

Operating temperature	-15 - 30 °C
-----------------------	-------------

##### Texts

Imprint	Without imprint
Installation mode	For screw fastening
Type of connection	With plug-in terminals

##### Suitable for

Hager cubyko	
--------------	--