



JG25BM\_IMG

**63A SP&N ENCLOSED MCCB 18kA**

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Functions**

Overvoltage protection	Yes
------------------------	-----

**Electric current**

Rated current	63 A
---------------	------

**Dimensions**

Depth	106 mm
Height	420 mm
Width	200 mm

**Cover, door**

Interlockable	No
Door/cover is transparent	No

**Materials**

RAL code	7035
Colour	Light grey
Material	Steel

**Connection**

Number of accessible phases	3
-----------------------------	---

**Scope of delivery**

Number of RCCB in enclosure	0
-----------------------------	---

**Equipment**

With socket outlet	No
--------------------	----

**Safety**

Ingress Protection (IP) class	IP3X
Protection class	Isolation class III
Number of earth leakage switches 300 mA	0