



FD52DN

Enclosure, NewVegaD, 900x550x193mm, 120 modules, surface-mounted, distribution

Technical Features

Voltage

Nominal voltage 230 - 400 V

Installation, mounting

Suitable for outdoor usage No

Mounting on Surface mounting

Electric current

Rated current 160 A

Equipment

Number of rails 5

Number of rows 5

With lock No

Has neutral terminal block No

Capacity

Number of modules 120

Dimensions

Height 900 mm

Width 550 mm

Depth 193 mm

Cover, door

Number of cabinet doors 0

Number of locks 0

Dimensions

Number of width units 24

Cover, door

Door/cover is transparent No

Connection

Number of conduit inlets 4

Materials

Material Metal
Plastic

RAL code 9010

Colour Pure white

Equipment

Has earthing terminal block Yes

Has mounting plate No

Safety

Protection class Isolation class II

Impact resistance IK IK07

Ingress Protection (IP) class IP30

Locking type Without lock

Sustainability

RoHS conform Yes