



VML1010

Dual Row HI Conf 8+10 Way 100A Switch 2*100A RCCB

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Functions

Has protection main switch	Yes
Overvoltage protection	No

Capacity

Number of modules	18
-------------------	----

Electric current

Rated current	100 A
---------------	-------

Dimensions

Depth	100 mm
Height	485 mm
Width	296.80 mm
Number of width units	18

Cover, door

Interlockable	No
Door/cover is transparent	No

Materials

RAL code	9010
Colour	Pure white
Material	Steel

Connection

Number of accessible phases	1
-----------------------------	---

Scope of delivery

Number of RCCB in enclosure	2
-----------------------------	---

Equipment

Number of rows	2
Number of rails	2
With socket outlet	No

Safety

Ingress Protection (IP) class	IP2XC
Number of earth leakage switches 300 mA	0

Sustainability

RoHS conform	Yes
--------------	-----