




75424004



Technical Features

Voltage	
Operating voltage over bus	21 - 32 V
Settings	
Supported configuration mode	ETS
Voltage	
Auxiliary tension	24 - 24 V
Frequency	
Frequency	50 - 60 Hz
Power	
Current consumption	170 mA
Use conditions	
Operating temperature	-5 - 45 °C
Capacity	
Number of modules	4
Sustainability	
REACH-SVHC free	Yes
RoHS conform	Yes